




LEGEND		All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare																	
Mapping Symbol	Description	HYBRID CORN						OPEN-POLLINATED VARIETIES (OPV)						AREA					
		WET SEASON			DRY SEASON			WET SEASON			DRY SEASON			ha	%				
		Nutrient Requirement N P ₂ O ₅ K ₂ O	Recommended Fertilizer Rate (bags/hectare)		Nutrient Requirement N P ₂ O ₅ K ₂ O	Recommended Fertilizer Rate (bags/hectare)		Nutrient Requirement N P ₂ O ₅ K ₂ O	Recommended Fertilizer Rate (bags/hectare)		Nutrient Requirement N P ₂ O ₅ K ₂ O	Recommended Fertilizer Rate (bags/hectare)							
N-P-K	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O	N	P ₂ O ₅	K ₂ O				
1	L-L-L	120	60	60	"Complete" Option: (1st Application): 8.5 (14-14-14); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 0.5 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 2.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 5 (16-20-0); 3.25 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);	80	60	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	60	"Complete" Option: (1-time Application): 8.5 (14-14-14); 1 (46-0-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 2 (0-0-60);	347	2.92
2	L-L-ML	120	60	45	"Complete" Option: (1st Application): 6.5 (14-14-14); 0.75 (46-0-0); 1.75 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 3.25 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	80	60	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	45	"Complete" Option: (1-time Application): 6.5 (14-14-14); 1.5 (46-0-0); 1.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1.5 (0-0-60);	439	3.70
3	L-L-MH	120	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 4 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	80	60	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 3.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 3.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 1 (0-0-60);	629	5.30
4	L-L-H	120	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 6 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 3.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	80	60	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 6 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 6 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	60	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 6 (0-18-0); "AmmoPhos" Option: (1-time Application): 6 (16-20-0); 1.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 6.75 (0-18-0); 0.25 (0-0-60);	677	5.71
5	L-ML-L	120	40	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 1 (46-0-0); 0.75 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	60	"Complete" Option: (1-time Application): 5.75 (14-14-14); 3.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 2 (0-0-60);	80	40	60	"Complete" Option: (1st Application): 5.75 (14-14-14); 0.75 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	60	"Complete" Option: (1-time Application): 5.75 (14-14-14); 1.75 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 2 (0-0-60);	253	2.13
6	L-ML-ML	120	40	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 3.5 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);	80	40	45	"Complete" Option: (1st Application): 5.75 (14-14-14); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	45	"Complete" Option: (1-time Application): 5.75 (14-14-14); 1.75 (46-0-0); 0.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1.5 (0-0-60);	274	2.31
7	L-ML-MH	120	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 4 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	80	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 0.5 (46-0-0); 1 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 2.25 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);	180	1.52
8	L-ML-H	120	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 4 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	80	40	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.5 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);	273	2.30
9	L-MH-L	120	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	80	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);	225	1.90
10	L-MH-ML	120	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	80	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);	152	1.28
11	L-MH-MH	120	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 4.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	80	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 2.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);	316	2.66
12	L-MH-H	120	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 2.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 2.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 2 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0); Single Element Option: (1st Application): 2.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 5 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 4.5 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 5.25 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	80	20	7	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.5 (0-18-0); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1 (46-0-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	20	7	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.5 (0-18-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2.75 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 2.25 (0-18-0); 0.25 (0-0-60);	74	0.62
13	L-H-L	120	0	60	Single Element Option: (1st Application): 2.75 (46-0-0); 2 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	60	Single Element Option: (1-time Application): 5.25 (46-0-0); 2 (0-0-60);	80	7	60	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	7	60	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 2 (0-0-60);	195	1.64
14	L-H-ML	120	0	45	Single Element Option: (1st Application): 2.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	45	Single Element Option: (1-time Application): 5.25 (46-0-0); 1.5 (0-0-60);	80	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 1.5 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.75 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.75 (46-0-0);	80	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 3.25 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 3.25 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 3.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);	75	0.63
15	L-H-MH	120	0	30	Single Element Option: (1st Application): 2.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.75 (46-0-0);	120	0	30	Single Element Option: (1-time Application): 5.25 (46-0-0); 1 (0-0-60);	80	7	30	"Complete" Option: (1st Application): 0.75 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 1.75 (46-0-0); Single Element Option: (1st Application): 1.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1						

All fertilizer recommendation options are recommended to apply additional 10-20 bags Organic Fertilizer per hectare																																			
Mapping Symbol	Description	HYBRID CORN										OPEN-POLLINATED VARIETIES (OPV)										AREA													
		WET SEASON					DRY SEASON					WET SEASON					DRY SEASON																		
		Nutrient Requirement					Nutrient Requirement					Nutrient Requirement					Nutrient Requirement					ha	%												
		N	P ₂ O ₅	K ₂ O	Recommended Fertilizer Rate (bags/hectare)			N	P ₂ O ₅	K ₂ O	Recommended Fertilizer Rate (bags/hectare)			N	P ₂ O ₅	K ₂ O	Recommended Fertilizer Rate (bags/hectare)			N	P ₂ O ₅			K ₂ O	Recommended Fertilizer Rate (bags/hectare)										
23	ML-NL-MH	100	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (46-0-0); 1 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 3 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);					60	40	30	"Complete" Option: (1st Application): 4.25 (14-14-14); 1 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	40	30	"Complete" Option: (1-time Application): 4.25 (14-14-14); 1.5 (46-0-0); 1 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 1 (0-0-60);					100	0.84
					"Complete" Option: (1st Application): 1 (14-14-14); 2 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);								"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);						
24	ML-ML-H	100	40	7	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	40	7	"Complete" Option: (1-time Application): 3 (14-14-14); 4 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);					60	40	7	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	40	7	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);					105	0.88
					"Complete" Option: (1st Application): 1 (14-14-14); 2 (46-0-0); 3.75 (0-18-0); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.75 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 4 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 3 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);								"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 3.75 (0-18-0); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 4 (16-20-0); 0.25 (0-0-60); (2nd Application): 1.25 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 3.75 (0-18-0); "AmmoPhos" Option: (1-time Application): 4 (16-20-0); 1.25 (46-0-0); 0.25 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 4.5 (0-18-0); 0.25 (0-0-60);						
25	ML-MH-L	100	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);					60	20	60	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	20	60	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);					138	1.16
					"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);								"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);								"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 2 (0-0-60);						
26	ML-MH-ML	100	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);					60	20	45	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	20	45	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);					14	0.12
					"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);								"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);								"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 1 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1.5 (0-0-60);						
27	ML-MH-MH	100	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);					60	20	30	"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); (0-0-60); (2nd Application): 1.5 (46-0-0);					60	20	30	"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);					77	0.65
					"Complete" Option: (1st Application): 3 (14-14-14); 1.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 2.25 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 1.5 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0); Single Element Option: (1st Application): 2.25 (46-0-0); 2.25 (0-18-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);								"Complete" Option: (1-time Application): 3 (14-14-14); 3.5 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 3.75 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 4.5 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);								"Complete" Option: (1st Application): 3 (14-14-14); 0.5 (46-0-0); 0.5 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 2 (16-20-0); 0.75 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 2.25 (0-18-0); (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 3 (14-14-14); 1.75 (46-0-0); 0.5 (0-0-60); "AmmoPhos" Option: (1-time Application): 2 (16-20-0); 2 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 2.25 (0-18-0); 1 (0-0-60);						
29	ML-H-L	100	0	60	Single Element Option: (1st Application): 2.25 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	0	60	Single Element Option: (1-time Application): 4.5 (46-0-0); 2 (0-0-60);					60	7	60	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 2.5 (46-0-0); 2 (0-0-60); Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	7	60	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 2 (0-0-60);					147	1.24
					Single Element Option: (1st Application): 2.25 (46-0-0); 2 (0-0-60); (2nd Application): 2.25 (46-0-0);								Single Element Option: (1-time Application): 4.5 (46-0-0); 2 (0-0-60);								"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 2.5 (46-0-0); 2 (0-0-60); Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 2 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 2 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 2 (0-0-60);						
30	ML-H-ML	100	0	45	Single Element Option: (1st Application): 2.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	0	45	Single Element Option: (1-time Application): 4.5 (46-0-0); 1.5 (0-0-60);					60	7	45	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	7	45	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);					130	1.10
					Single Element Option: (1st Application): 2.25 (46-0-0); 1.5 (0-0-60); (2nd Application): 2.25 (46-0-0);								Single Element Option: (1-time Application): 4.5 (46-0-0); 1.5 (0-0-60);								"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 1.25 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 1.25 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1.5 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1.5 (0-0-60);						
31	ML-H-MH	100	0	30	Single Element Option: (1st Application): 2.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	0	30	Single Element Option: (1-time Application): 4.5 (46-0-0); 1 (0-0-60);					60	7	30	"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 0.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);					60	7	30	"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);					42	0.35
					Single Element Option: (1st Application): 2.25 (46-0-0); 1 (0-0-60); (2nd Application): 2.25 (46-0-0);								Single Element Option: (1-time Application): 4.5 (46-0-0); 1 (0-0-60);								"Complete" Option: (1st Application): 1 (14-14-14); 1 (46-0-0); 0.75 (0-0-60); (2nd Application): 1.5 (46-0-0); "AmmoPhos" Option: (1st Application): 0.75 (16-20-0); 1 (46-0-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0); Single Element Option: (1st Application): 1.5 (46-0-0); 0.75 (0-18-0); 1 (0-0-60); (2nd Application): 1.5 (46-0-0);								"Complete" Option: (1-time Application): 1 (14-14-14); 2.5 (46-0-0); 0.75 (0-0-60); "AmmoPhos" Option: (1-time Application): 0.75 (16-20-0); 2.5 (46-0-0); 1 (0-0-60); Single Element Option: (1-time Application): 2.75 (46-0-0); 0.75 (0-18-0); 1 (0-0-60);						
32	ML-H-H	100	0	7	Single Element Option: (1st Application): 2.25 (46-0-0); 0.25 (0-0-60); (2nd Application): 2.25 (46-0-0);					100	0																								

Mode of Application of Fertilizer

Wet Season

First Application: Apply all the recommended phosphate and potash and 1/2 of Nitrogen fertilizer in a band about 2 inches to the sides of and about 2 inches below the seed during planting.

Second Application: Side-dress the remaining 1/2 Nitrogen fertilizer when the plants are about four (4) weeks old or when the plants are knee high (12-19 inches high). Hilling up is recommended after the application of the fertilizer for better growth development.

Dry Season

Apply all the recommended fertilizers at planting or three (3) weeks after planting. Hilling up is recommended after the application of the fertilizer for better growth development.